

**Soprano Titanium Painless 755 808 1064 Triple wavelength diode laser
hair removal machine**



Hair Removal, Reinvented.

A breakthrough hair removal platform that combines ultimate functionality with unparalleled comfort. Soprano Titanium leverages the benefits of three combined wavelengths, with an improved patient experience and a business-oriented approach, creating a unique and result-driven new solution in the world of professional hair removal.



- Quattro - A breakthrough applicator with an especially large spot size of 4cm²
- An advanced ICE Plus technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment
- Includes two connectors, which enables two different applicators to be connected to the platform at all times
- Equipped with a new large sized 15" Android screen, with preset parameters, which enables to enjoy a more intuitive, userfriendly work experience



Exceptionally Large Spot Size

Quick and Comfortable

This machine features Quattro 3D, a unique and efficient new applicator with an especially large spot size of 4cm², for faster treatments and better patient experience.

IVYICE Plus

Continuous Contact Cooling

IVYICE Plus is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.



Dual Connector

More Flexibility. Less Fuss.

This machine is the first version of hair removal systems that includes two connectors, which enables two different applicators to be connected to the platform at all times.

Multiple Options for Handle's Spot Size

We have a lot of different spot sizes of handle for options, to satisfy the different needs of our clients. The higher the power of the machine, the more selectivity of the handle.

Difference between Micro-channel and Macro-channel

Micro-channel and Macro-channel are all internal structure types in diode laser modules,

the difference is that each of them affects the different levels of heat dissipation efficiency in a diode laser.

With a Micro-channel diode laser module, the handle can have a higher level of heat dissipation efficiency than the macro-channel diode laser module. That means the handle will have a longer lifetime and more stable performance during daily use.



Water-cooling circulation pass through the entire diode laser, not a single laser bar.



Water-cooling circulation pass through every laser bar.

Machine Customization

We can offer services like customization of machine case in a color you choose, placement of your brand's logo in our machine, selection power of diode laser module in handle you want.

System supports different languages

The hair removal system supports multiple languages, for languages the system doesn't support now, we can customize and add support for you.

Design your own case

If you have needs about your own brand's machine, we have professional ID designers to make design for you.

Warranty support all the time

Our R&D team has rich experience in Beauty equipment, always ready to help you solve the problem.



1. Machine color customization



2. System language customization



3. Design your own machine



4. Warranty support all the time



SPECIFICATION

Power	1200w	2000W
Spot size	15x20mm	15*30mm
Wavelength	755+808+1064nm 3 in 1	
Fluency	Up to 120J	
Pulse frequency	Up to 10Hz	
Pulse duration	10~400ms	
Laser bars	Germany power-exponent function laser bar	
System language	ALL language support	

Display size	15.6"
Input VAC	AC230V ± 10%, 15A 60 / 50Hz / AC110V ± 10%, 60Hz (Optional)
Packing box	70(L)x64(W)x132(H)cm
Gross Weight	119kg

PACKING & DELIVERY

Packing list of Germany bar 808nm permanent and painless diode 810 laser hair removal



Machine



Applicator



Applicator support



Footswitch



Power cable



Key



Funnel & Water pipe



Bibcock



Screw



Protect glasses
Customer glasses



1

Cleaning



2

Aluminum road case
with well-cut padding



3

Protective
covering



4

Pcak the aluminium
case and firm with stripes



5

Delivery